

The GW Mini Dehumidifier Series

Reusable and Non-Consumable
Eco-Friendly & Non-hazardous

The GW mini dehumidifier series are multi-national patented and reusable.

Product Concept:

The mini dehumidifier works by using high molecular moisture absorbing granules to absorb surrounding humidity inside cabinets, closets and drawers etc... When complete with moisture absorption, simply plug into socket for recharging procedure to use the dehumidifier again.

Advantageous features comparing to solvent dehumidifying products:


- **Effective** : Constantly eliminates moisture damage
- **Eco-friendly and safe** : No hazardous refills needed
- **Non-Toxic and odorless** : Dissolvent, no water or hazardous liquid
- **Economical** : regenerate when the indicator changes color




Product application:



Closets



Safes



Cabinets



Storage Boxes

Instruction & Regeneration

When the dampness absorbing granules in the indicator show blue, the dehumidifier is ready to be used for dehumidification. When the granules inside the indicator turn pink, it means that the dehumidifier needs to be regenerated. By being plugged into a socket for 12 hours to fully release the dampness, the dehumidifier will be ready to be re-used when the granules in the indicator turn back to blue.



Dampness absorbing granules turn pink



Leave the unit plugged in for regenerate



Dampness absorbing granules turn back to blue, the regeneration is complete.



The GW Reusable Dehumidifying Bag series

Reusable and Non-Consumable
Eco-Friendly & Non-hazardous

The GW Reusable dehumidifying bag series are multi-national patented and are offered with smart color changing indicators to tell when to regenerate the bags for reuse.

Product Concept:

The reusable dehumidifying bag works by using high molecular moisture absorbing granules to absorb surrounding humidity inside cabinets, closets and drawers etc...
When complete with moisture absorption, simply put into microwave oven for regeneration, then the dehumidifying bag can be used again.

Advantageous features comparing to solvent dehumidifying products:

- **Effective** : Constantly eliminates moisture damage
- **Eco-friendly and safe** : No hazardous refills needed
- **Non-Toxic and odorless** : Dissolvent, no water or hazardous liquid
- **Economical** : regenerate when the indicator changes color

Product application:



Closets



Safes



Cabinets



Storage Boxes


Instruction & Regeneration

When the color picture indicator shows blue, the dehumidifying bag is ready for use in any confined space.
When the color picture indicator turns pink, it means that the dehumidifying bag needs to be regenerated.
By being placed inside a microwave oven heating for 3 ~ 5 minutes to fully release the dampness, the dehumidifying bag will be ready to be re-used when the color picture indicator turns back to blue.



Civi-Health®


Dehumidifying Egg




The touch of nonstop comfort

The award winning product for
"2004 Innovation product award" by
Taiwan External Trade Development
Council.

The complete dehumidifying satisfaction



Model No : E-200-1



Model No : E-200